



# Service manual

## Optical Encoder ME 22



### Index

	Pag.
Description	2
Features	2
Ordering information	2
Recommended operating conditions	3
Limiti massimi di utilizzo	3
Dimensions	4
Electrical interface	4
Mechanical notes	5
Mounting considerations	5
ME22 mounting instructions	6
Available accessories	8



### MANUFACTURER INFORMATION

THIS DOCUMENT AND ANY ASSOCIATED DATA CONTAIN RESTRICTED INFORMATION THAT IS PROPERTY OF THE MANUFACTURER AND MAY NOT BE DISCLOSED OR DUPLICATED FOR OTHERS EXCEPT AS AUTHORIZED BY THE MANUFACTURER. INFORMATION CONTAINED IN THIS PUBLICATION MAY BE SUPERSEDED BY UPDATES. IT IS YOUR RESPONSIBILITY TO ENSURE THAT YOUR APPLICATION MEETS WITH YOUR SPECIFICATIONS.

# Optical Encoder ME22

## Description

The ME 22 is a optical incremental encoder, He is a reliable low cost hollow shaft encoder that can be fixed quickly and easily on different sizes of motor shafts.



The encoder provides two square wave outputs in quadrature (90 degrees phase shifted) for counting and direction . The resolution of the encoder is determined by the number of counts per revolution (CPR). The power supply and signals they are provided by a 5-pin Molex connector.

## Features

- Small size: 22.0 mm diameter x 21.9 mm length
- Quick and easy assembly without coming into contact with sensitive components
- Output channels: 2 (quadrature) + 1 index-channel optional
- Power supply: 5 VDC
- Output type: TTL Compatible.
- Output circuit: pull up
- Resolution: up to 360 CPR (counts per revolution)
- Max. shaft diameter: 9,525 mm (3/8")
- Operating temperature: -20 °C to +85 °C.
- Frequency: 60 kHz.
- Compliant EU-directive 2002/95/EG (RoHS)

## Ordering information

ME22	100	6.000	2	LS																																								
	<table border="1"><tr><td>Encoder Resolution (CPR)*</td></tr><tr><td>001 **</td></tr><tr><td>002 **</td></tr><tr><td>004 **</td></tr><tr><td>008 **</td></tr><tr><td>050 ***</td></tr><tr><td>064 ***</td></tr><tr><td>100</td></tr><tr><td>108</td></tr><tr><td>120</td></tr><tr><td>124</td></tr><tr><td>128</td></tr><tr><td>150</td></tr><tr><td>160</td></tr><tr><td>200</td></tr><tr><td>250</td></tr><tr><td>256</td></tr><tr><td>300</td></tr><tr><td>360</td></tr></table>	Encoder Resolution (CPR)*	001 **	002 **	004 **	008 **	050 ***	064 ***	100	108	120	124	128	150	160	200	250	256	300	360	<table border="1"><tr><td>Motor Shaft Diameter (mm)</td></tr><tr><td>1.500</td></tr><tr><td>2.000</td></tr><tr><td>2.300</td></tr><tr><td>2.500</td></tr><tr><td>3.000</td></tr><tr><td>3.175 (1/8")</td></tr><tr><td>3.969 (5/32")</td></tr><tr><td>4.000</td></tr><tr><td>4.763 (3/16")</td></tr><tr><td>5.000</td></tr><tr><td>6.000</td></tr><tr><td>6.350 (1/4")</td></tr><tr><td>8.000</td></tr><tr><td>9.000</td></tr><tr><td>9.525 (3/8")</td></tr></table>	Motor Shaft Diameter (mm)	1.500	2.000	2.300	2.500	3.000	3.175 (1/8")	3.969 (5/32")	4.000	4.763 (3/16")	5.000	6.000	6.350 (1/4")	8.000	9.000	9.525 (3/8")	<table border="1"><tr><td>Number of channels</td></tr><tr><td>1 = 1 Channel</td></tr><tr><td>2 = 2 Channel</td></tr></table>	Number of channels	1 = 1 Channel	2 = 2 Channel	<table border="1"><tr><td>Output option</td></tr><tr><td>LS = Connector + standard cable</td></tr></table>	Output option	LS = Connector + standard cable
Encoder Resolution (CPR)*																																												
001 **																																												
002 **																																												
004 **																																												
008 **																																												
050 ***																																												
064 ***																																												
100																																												
108																																												
120																																												
124																																												
128																																												
150																																												
160																																												
200																																												
250																																												
256																																												
300																																												
360																																												
Motor Shaft Diameter (mm)																																												
1.500																																												
2.000																																												
2.300																																												
2.500																																												
3.000																																												
3.175 (1/8")																																												
3.969 (5/32")																																												
4.000																																												
4.763 (3/16")																																												
5.000																																												
6.000																																												
6.350 (1/4")																																												
8.000																																												
9.000																																												
9.525 (3/8")																																												
Number of channels																																												
1 = 1 Channel																																												
2 = 2 Channel																																												
Output option																																												
LS = Connector + standard cable																																												

\*: other resolutions  
encoder on request  
\*\*:only two channels  
\*\*\*: only one channel



Preferential codes

## Available accessories, see page. 8

- cable 300 mm length (UL1061 / AWG28)
- centering gauge (not included as standard part)
- fastening screws DIN 84 M1.6x3

**Recommended operating conditions**

Electrical characteristics are only effective for the range of the operating temperatures.  
Standard values at 25 °C and VDC = 5 V ± 5%.



Parameter	Symbol	Nominal	Min.	Max.	Unit	Notes
Operating temperature	T <sub>A</sub>	+25	- 20	+85	° C	
Supply voltage	V <sub>DC</sub>	5.0	4.5	5.5	V <sub>DC</sub>	
Supply current (two channels)	I <sub>CC</sub>	15	13	18	mA	
Line capacity (admissible value)	C <sub>L</sub>			100	pF	internal pull-up 2.7 kΩ
Count frequency	f			60	kHz	rpm x N / 60 x 10 <sup>-3</sup>
<b>A and B Channel</b>						
High level output voltage (standard version)	V <sub>OH</sub>		2.4		V <sub>DC</sub>	I <sub>OH</sub> = -0.2 mA
Low level output voltage (standard version)	V <sub>OL</sub>			0.4	V <sub>DC</sub>	I <sub>OL</sub> = 8 mA
Rise time (standard version)	T <sub>r</sub>	500/(7)*			ns / (μs)*	C <sub>L</sub> = 25 pF
Fall time (standard version)	T <sub>f</sub>	100/(1.3)*			ns / (μs)*	R <sub>L</sub> = 2.7 kΩ

\* only for 1, 2, 4, 8 CPR

**Absolute maximum ratings**


Environment	Symbol	Min.	Max.	Unit	Notes
Storage temperature	T <sub>S</sub>	- 40	+ 85	° C	
Operating temperature	T <sub>A</sub>	- 20	+ 85	V <sub>DC</sub>	
Humidity exposure			90	% RH	not codensing
Supply voltage	V <sub>DC</sub>	- 0.5	7	V <sub>DC</sub>	
Output voltage	V <sub>O</sub>	- 0.5		V <sub>DC</sub>	
Output current for channel	I <sub>OUT</sub>	- 1.0	8	mA	
Vibration			2000	Hz	20 g

**ATTENTION****ESD Warning: (Electrostatic discharges):**


handle with care to avoid damaging the sensor with electrostatic discharges

# Optical Encoder ME22

## Dimensions



## Electrical interface



### Definitions:

- **CPR** - Counts per Revolution: number of notches on the optical disc or periods per rotation of the encoder.
- **C** - One cycle: 360 electrical degrees ( $^{\circ}\text{e}$ ), one period of the signal.
- **P** - Pulse Width: The number of electrical degrees that an output is high during one cycle. This value is nominally  $180\text{ }^{\circ}\text{e}$  or half a cycle.
- **S** - State Width: The number of electrical degrees between a transition in the output of channel A and the neighbouring transition in the output of channel B. There are 4 states per cycle, each nominally  $90\text{ }^{\circ}\text{e}$
- **$\varphi$**  - Phase: The number of electrical degrees between the centre of the high state of channel A and the center of the high state of channel B. This value is nominally  $90\text{ }^{\circ}\text{e}$  .
- **$\Delta Q$**  - Position error: angular difference between the current angular position of the shaft and the position indicated by the encoder cycle count

### A and B channel encoding features:

Parameter	Symbol	Nominal	Max Error	Unit
Pulse width	P	180	$\pm 70$	$^{\circ}\text{e}$
Phase error	$\varphi$	90	$\pm 60$	$^{\circ}\text{e}$


## Mechanical notes



Parameter	Symbol	Value	Tolerance	Unit
Outer dimensions		$\varnothing 22,0 \times 21,9$	-	mm
Shaft diameter	$\varnothing w$	1,5 / 2,0 / 2,3 / 2,5 / 3,0 / 3,175 / 3,969 / 4,0 4,763 / 5,0 / 6,0 / 6,35 / 8,0 / 9,0 / 9,525	$\pm 0,01$	mm
Required shaft length	$L_w$	9,5	+ 2,0	mm
Max. allowable axial shaft play of motor		0,6	-	mm
Max. allowable radial shaft play of motor		0,025	-	mm
Mounting screw size (DIN 84)		M1,6	-	-
Tightening torque of the screws		15	- 5	Ncm
Pitch circle diameter	$\varnothing c$	17,0	$\pm 1,0$	mm
Flange inside bore diameter	$\varnothing z$	7,1 o 10,1	+ 0,03	mm
Mounting boss diameter	$\varnothing m$	7,1	- 0,03	mm
Max. mounting boss height	$h_z$	1,5	- 0,1	mm
Mating connector (Molex)		5 pin 50079-8000 housing 51021-0500	-	
Total weight		7	-	g
Moment of inertia of the hub with the magnet		5,2	$\pm 1,0$	$\text{g} \cdot \text{mm}^2$
Protection grade according to DIN 40500		IP50	-	-

## Mounting considerations

The ME22 encoder is designed to self align by using a mounting boss. You need a tool centering gauge. The drawing shows the configuration of the mounting boss along with the location of the mounting screw holes. Shaft diameter and tolerances are given in the above mentioned chart.




# Optical Encoder ME22

## ME22 mounting instructions




1



Align the base plate to the motor shaft using the centering tool

2



Then fix the base plate to the motor flange using two screws

3



Align the housing to the base plate and slide it over the latter

4




The hub is thus automatically centered on the motor shaft

5



From this position the housing cannot be locked

6



Press the housing into the final position

## ME22 mounting instructions



7



The housing can now be locked

8



Turn the housing into its final position, the encoder is now ready for use

## WARNING



**DO NOT ROTATE AND PULL OUT THE ENCODER AFTER ASSEMBLY OR WHEN IT IS IN OPERATION.**

## ATTENTION


The encoder is designed that it may be assembled only one time, otherwise the guarantee will be voided. Note:  
see IMPOR-TANT NOTICE (page 8)

# Optical Encoder ME22

## Available accessories



- Standard cable length 300 mm (UL 1061 / AWG 28)



- Centering gauge for centering the ME base plate on the motor flange or an adapter plate



- Screws DIN84 M1.6 X 3



## IMPORTANT NOTICE

The encoder is designed that it may be assembled only one time, otherwise the guarantee will be voided. The guarantee will be voided by misuse, accident, modification, unsuitable physical or operating environment, operation in other than the specified operating environment, or failure caused by a product for which the manufacturer is not responsible.

The manufacturer reserves the right to make corrections to its products and services also data